

Air duct temperature Probe Type 23 NiCr-Ni Type K


Product-Data

Sensor element:	Type K NiCr-Ni Class 1
Temperature range:	-50...+400 °C
Installation length:	200 mm
Diameter Installation length:	6 mm
Probe tube material:	Stainless steel 1.4571 / 1.4403
Connecting cable:	PVC insulated Ø 4 mm / 2 x 0.22 mm ²
Connecting cable length:	2 meters
Tmax connecting cable	+80 °C
Plug:	open wire ends
Accuracy:	Class 1 DIN IEC 60584 +/- 1.5 °C

Order-Information

TSG-Order-Number:	8006 1530
Conrad-Order-Number:	50 78 05-XX

Dimensions



Picture



example of installation

