



Sample photo

Order symbol: PCM 95/75 G
Product nbr: 6016332
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074054784
EI. number:
 Finland 3421394
 Denmark 8212027585

Including: Base with metric knock-outs and PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:			L		W		H		Rating:	
mm:	100	100	75					Ingress Protection (EN 60529): IP 66/67		
inch:	3.9	3.9	3					Impact Resistance (EN 50102): IK 08		
Materials:										
Material:	PC									
Base colour:	RAL 7035									
Cover colour:	RAL 7035									
Cover screws material:	Polyamide									
Cover screws colour:	Grey									
Gasket material:	Polyurethane									
Temperatures:										
Short term:	-40 ... 120 °C									
Continuous:	-40 ... 80 °C									
Short term:	-40 ... 250 °F									
Continuous:	-40 ... 175 °F									
Accessories:										
MIV 95	Mounting plate									
B-3	DIN-35 Mounting rail									
Rating:										
Electrical insulation: Totally insulated										
Halogen free (DIN/VDE 0472, Part 815): Yes										
UV resistance: UL 508										
Flammability Rating (UL 746 C 5): UL 94 5V										
Glow Wire Test (IEC 695-2-1) °C: 960										
NEMA Class: NEMA 1, 4, 4X, 6, 12, 13										
Certificates:										
Germanischer Lloyd (GL)										
Underwriters Laboratories										
Det Norske Veritas										
Fimko										
Europe EN 50298 1998										
UL Canada										
Gost R										

