



Sample photo

Order symbol: PCM 175/125 T
Product nbr: 6016922
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074052261
EI. number:
 Finland 3435220
 Denmark 8212027530
 Sweden 2535440

Including: Base with metric knock-outs and TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:		L	W	H	Rating:
mm:		180	180	125	Ingress Protection (EN 60529): IP 66/67
inch:		7.1	7.1	4.9	Impact Resistance (EN 50102): IK 08
Materials:					
Material:		PC			
Base colour:		RAL 7035			
Cover colour:		Smoked grey			
Cover screws material:		Polyamide			
Cover screws colour:		Black			
Gasket material:		TPE			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MIV 175		Mounting plate			
MIN 15		DIN-15 Mounting rail			
MIV 15		DIN-35 Mounting rail			
FP A 175/180		Front plate			
HFP 180		Front plate hinge series			
Certificates:					
		Germanischer Lloyd (GL)			
		Underwriters Laboratories			
		Det Norske Veritas			
		Fimko			
		Europe EN 50298 1998			
		UL Canada			
		Gost R			
		Electrical insulation: Totally insulated			
		Halogen free (DIN/VDE 0472, Part 815): Yes			
		UV resistance: UL 508			
		Flammability Rating (UL 746 C 5): UL 94 5V			
		Glow Wire Test (IEC 695-2-1) °C: 960			
		NEMA Class: NEMA 1, 4, 4X, 6, 12, 13			

