



Sample photo

**Order symbol:** PCM 200/75 T  
**Product nbr:** 6016926  
**Description:** Enclosure, PC  
**Remarks:** Smoked transparent cover

**EAN:** 6418074038319  
**EI. number:**  
 Finland 3421676  
 Denmark 8212027297  
 Sweden 2535445

**Including:** Base with metric knock-outs and TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:		L	W	H	Rating:
mm:		255	180	75	<b>Ingress Protection (EN 60529):</b> IP 66/67
inch:		10	7.1	3	<b>Impact Resistance (EN 50102):</b> IK 08
Materials:					
<b>Material:</b>	PC				
<b>Base colour:</b>	RAL 7035				
<b>Cover colour:</b>	Smoked grey				
<b>Cover screws material:</b>	Polyamide				
<b>Cover screws colour:</b>	Black				
<b>Gasket material:</b>	TPE				
Temperatures:					
<b>Short term:</b>	-40 ... 120 °C				
<b>Continuous:</b>	-40 ... 80 °C				
<b>Short term:</b>	-40 ... 250 °F				
<b>Continuous:</b>	-40 ... 175 °F				
Accessories:					
MIV 200	Mounting plate				
MIN 15	DIN-15 Mounting rail				
MIN 20	DIN-15 Mounting rail				
MIV 15	DIN-35 Mounting rail				
MIV 20	DIN-35 Mounting rail				
FP A 200/180	Front plate				
HFP 180	Front plate hinge series				
					<b>Electrical insulation:</b> Totally insulated
					<b>Halogen free (DIN/VDE 0472, Part 815):</b> Yes
					<b>UV resistance:</b> UL 508
					<b>Flammability Rating (UL 746 C 5):</b> UL 94 5V
					<b>Glow Wire Test (IEC 695-2-1) °C:</b> 960
					<b>NEMA Class:</b> NEMA 1, 4, 4X, 6, 12, 13
Certificates:					
		Germanischer Lloyd (GL)			
		Underwriters Laboratories			
		Det Norske Veritas			
		Fimko			
		Europe EN 50298 1998			
		UL Canada			
		Gost R			

