





| REV. | MODIFICATION. | DATE | DRN |
|------|---------------|----------|-----|
| 01 | NEW DRAWING | 08/08/06 | NJB |
| 02 | CO2010985 | 01/10/10 | SF |
| 03 | CO2011038 | 14/01/11 | SF |





1.5 Ts




2 Ts




2.5 Ts



2x1.5 Ts



3 Ts



NOTES.

- 1) See drawing 06-087 sheet 2 of 2 for Impedance graphs.
- 2) Impedance figures are typical values.
- 3) other sizes available by special order.
- 4) Packaging information is only a guide & subject to variation.

| Ferrite Material: K5B - A6 RMS-303 • Glue RMS-301 • Wires RMS-306 | | | | | | | |
|---|-----------|-----------|-----------|--------------|--------|---------------------------|-----------------|
| RRH6 & RRH8 | A (mm) | B (mm) | C (mm) | IMPEDANCE(Ω) | | Standard Pack (Pieces) | Number of Turns |
| | | | | 25MHz | 100MHz | | |
| RRH6-1-15-K5B | 6.00 | 10.00 | 0.85 | 390 | 460 | 500 | 1.5 |
| RRH6-1-20-K5B | 6.00 | 10.00 | 0.85 | 510 | 580 | 500 | 2 |
| RRH6-1-20-A6 | | | | | | | |
| RRH6-1-25-K5B | 6.00 | 10.00 | 0.85 | 690 | 680 | 500 | 2.5 |
| RRH6-2-15-K5B | 6.00 | 10.00 | 0.85 | 340 | 450 | 500 | 2x1.5 |
| RRH6-1-30-K5B | 6.00 | 10.00 | 0.85 | 860 | 750 | 500 | 3 |







INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.

RICHCO, INC.
WWW.RICHCO-INC.COM

ALL DIMENSIONS IN MM
GENERAL TOLERANCES ±0.25
UNLESS OTHERWISE STATED
1 DECIMAL PLACE ±
2 DECIMAL PLACES ±
ANGULAR ±1°

| | | | |
|--|------------------|-----------------------|------------------|
| MATERIAL: See Table | | COLOUR: See Table | |
| DESCRIPTION: RRH6 Ferrite Wound Beads | | PART No: See Table | |
| DRG No: 06-087 | NPR No: | Mass:(g) | SHEET SIZE A3 |
| DRN NJB | DATE 08/08/06 | CHKD AS | DATE 08/08/06 |
| SCALE NTS | | SHEET No. 1 OF 2 | |

| REV. | MODIFICATION. | DATE | DRN |
|------|---------------|----------|-----|
| 01 | NEW DRAWING | 08/08/06 | NJB |
| 02 | CO2010985 | 01/10/10 | SF |
| 03 | CO2011038 | 14/01/11 | SF |



NOTES.
1) Impedance figures are typical values.

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.

RICHCO, INC.
WWW.RICHCO-INC.COM

DESCRIPTION:
RRH6 Ferrite Wound Beads, Impedance Graphs.

| | | | |
|--------------------------|-------------------------|----------------------------|---------------------|
| DRG No: 06-087 | | SHEET SIZE A3 | |
| DRN NJB | DATE 08/08/06 | CHKD AS | SCALE NTS |
| DATE 08/08/06 | | SHEET No. 2 OF 2 | |