


Non-Slip Tape

ANST25/10M



Specification

Structure	: PVC, Quartz sand
Tape Length	: 10M \pm 1%
Tape Width	: 50mm \pm 0.5mm
Total thickness	: 1mm \pm 0.2mm
Color	: Black

Technical Data

Tack Rolling Ball	: \geq 13#
Adhesive power	: \geq 8N/25mm
Tensile strength	: $>$ 50N/25mm
Elongate Rate	: $>$ 30%
Operating temperature	: -10°C ~ 40°C