

EFB

Induct Fans (100 & 125mm)

100mm & 125mm induct fans
IPX4 rated



Accessories

GG42/GG82

100 & 125mm external louvred wall vent available in white or brown.



Flexiduct


Flexible 100 & 125mm PVC ducting (including 2 plastic fixing clips).



Physical Specifications


Weight: 100mm fan – 0.44kg
125mm fan – 0.49kg
Material: White gloss finish ABS plastic

Dimensions



	A	B
100mm	110	99
125mm	110	115

Performance Graph



Electrical Specifications

230V~50Hz Class II
Consumption: EFB100 – 18W
EFB125 – 20W
Cabling: 1mm² max.

Data Table

	Performance in free air m³/h ¹	Sound Pressure level @ 3m Ls ⁻¹	dB(A)	IP Rating	Operation	Features
EFB100	110	30	31	X4	Single Speed	Basic
EFB125	200	56	42.4	X4	Single Speed	Basic