

## Digital Light Meter

- Designed to measure a wide range of lighting types
- Auto or manual ranging
- Cosine and color-corrected measurements
- Max function
- Hold function
- Auto zero adjustment
- Tethered sensor for remote measurements





The Digital Light Meter from IDEAL simply and accurately measures light levels from fluorescent, metal halide, high-pressure sodium and incandescent light sources. The intuitive design is the perfect “must-have” instrument for basic lighting audits to address safety, productivity and energy efficient needs.



## Features

- Measures all visible light sources
- Measures LED lighting
- Measures in four ranges up to 20,000 FC or 200,000 Lux
- +/- 3% basic accuracy
- Data hold mode
- Max reading mode
- Auto zero adjustment
- Low battery indication
- Auto power off
- Remote sensor with 59 in. (1.5m) cable

Description	Cat. No.
Digital Light Meter (case included)	61-686



## Innovation with a Purpose.

IDEAL INDUSTRIES, INC.  
1375 Park Avenue, Sycamore, IL 60178, USA / 815-895-5181 • 800-435-0705 in USA

International offices:  
Australia • Brazil • Canada • China • Germany • Mexico • UK  
For complete sales office contact information, visit us at:  
[www.idealindustries.com](http://www.idealindustries.com) • [www.testersandmeters.com](http://www.testersandmeters.com)