


Connection line DCF – Receiver BN 641138

Frankfurt



pull up resistance
if necessary

$$R \geq U_B: \quad 1 \text{ mA}$$

- 1: Earth
- 2: + operating voltage 1.2 ... 1.5 V-
- 3: DCF output
- 4: DCF output inverted

Outputs 3 and 4 of open collectors npn
max. 30 V 1 mA