

# Mounting base housing - BC 17,8 UT HBUS BK - 2896241

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Lower part for installation housing BC 17,8...



## Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4046356096690

## Technical data

### General

<b>Housing type</b>	Installation component housing
<b>Housing material</b>	polycarbonate
<b>Color</b>	black

### Ambient conditions

<b>Ambient temperature (operation)</b>	-40 °C ... 100 °C
--	-------------------

### Dimensions

<b>Length</b>	89.7 mm
<b>Constructional height</b>	49 mm
<b>Width</b>	17.8 mm

### Technical data

<b>Inflammability class according to UL 94</b>	V0
<b>Power dissipation at 20°C in the horizontal mounting position</b>	2.95 W

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27180401
<b>eCl@ss 4.1</b>	27180401
<b>eCl@ss 5.0</b>	27180506
<b>eCl@ss 5.1</b>	27180506
<b>eCl@ss 6.0</b>	27180802
<b>eCl@ss 7.0</b>	27182702
<b>eCl@ss 8.0</b>	27182702

# Mounting base housing - BC 17,8 UT HBUS BK - 2896241

## classifications

### ETIM

<b>ETIM 2.0</b>	EC001031
<b>ETIM 3.0</b>	EC001031
<b>ETIM 4.0</b>	EC001031
<b>ETIM 5.0</b>	EC001031

### UNSPSC

<b>UNSPSC 6.01</b>	31261501
<b>UNSPSC 7.0901</b>	31261501
<b>UNSPSC 11</b>	31261501
<b>UNSPSC 12.01</b>	31261501
<b>UNSPSC 13.2</b>	31261501




## approvals

---

UL Recognized / GOST / GOST /

---

### Approval details



## Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>