

Display module - EMG 22-LED 7S/24 - 2952305

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Indicator module, with 7 red LEDs and common return line, input voltage 24 V DC

The illustration shows version EMG 22-LED 7S/ 5



Key commercial data

| | |
|------------------|---------------|
| package_quantity | 10 |
| GTIN | 4017918084400 |

Technical data

Dimensions

| | |
|--------|---------|
| Width | 22.5 mm |
| Height | 75 mm |
| Depth | 47.5 mm |

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 45 °C |
| Ambient temperature (storage/transport) | -40 °C ... 60 °C |

General

| | |
|--------------------------------------|---------------------------|
| Input voltage | 24 V DC |
| Current required per light indicator | approx. 3 mA |
| Status display | 7 LEDs |
| Mounting position | Any |
| Assembly instructions | In rows with zero spacing |

Connection data

| | |
|--|---------------------|
| Conductor cross section solid min. | 0.2 mm ² |
| Conductor cross section solid max. | 4 mm ² |
| Conductor cross section stranded min. | 0.2 mm ² |
| Conductor cross section stranded max. | 2.5 mm ² |
| Conductor cross section AWG/kcmil min. | 24 |
| Conductor cross section AWG/kcmil max | 12 |
| Stripping length | 8 mm |

Display module - EMG 22-LED 7S/24 - 2952305

Technical data

Connection data

| | |
|--------------------------|------------------|
| Screw thread | M3 |
| Connection method | Screw connection |

classifications

eCl@ss

| | |
|-------------------|----------|
| eCl@ss 4.0 | 27210301 |
| eCl@ss 4.1 | 27210301 |
| eCl@ss 5.0 | 27210301 |
| eCl@ss 5.1 | 27210301 |
| eCl@ss 6.0 | 27210301 |
| eCl@ss 7.0 | 27210301 |
| eCl@ss 8.0 | 27210301 |

ETIM

| | |
|-----------------|----------|
| ETIM 2.0 | EC001432 |
| ETIM 3.0 | EC001597 |
| ETIM 4.0 | EC001597 |
| ETIM 5.0 | EC001767 |

UNSPSC

| | |
|----------------------|----------|
| UNSPSC 6.01 | 30211506 |
| UNSPSC 7.0901 | 39121008 |
| UNSPSC 11 | 39121008 |
| UNSPSC 12.01 | 39121008 |
| UNSPSC 13.2 | 39121008 |

approvals

GOST /

Approval details



Display module - EMG 22-LED 7S/24 - 2952305

accessories

EMG-GKS 12 - 2947035



Drawings

Circuit diagram

