

AL-28SP12-PT (Artikel-Nr. 710034-07)

EKULIT


SPECIFICATIONS:

TYPE	UNIT	AL-28SP12-PT
• Min. Sound Output at 30cm	dB	85
Rated Voltage	V _{DC}	12
Operating Voltage	V _{DC}	8~15
Resonant Frequency	Hz	2900±300
• Max. Current Consumption	mA	15
Operating Temperature	°C	-20~+60
Storage Temperature	°C	-30~+70
Weight	g	10

• Value applying at rated voltage DC

DIMENSIONS :

(Unit: mm)



Frequency response:

