

Technical datasheet: FT-27T-4.0A1-470

Specifications:

Resonant Frequency	4.0kHz \pm 0.5kHz
Max Resistance (Zr)	200 Ω
Capacitance	25000nF \pm 30%nF

Dimensions:

Type A: (D: \varnothing 27mm, d: \varnothing 20mm, T: 0.43mm, t: 0.20mm)

