

Technical datasheet: FT-34.7G-2.9B1-474

Specifications:

Resonant Frequency	2.8kHz \pm 0.5kHz
Max Resistance (Zr)	300 Ω
Capacitance	30000nF \pm 30%nF

Dimensions:

Type B: (D: \varnothing 34.7mm, d: \varnothing 25.0mm, T: 0.50mm, t: 0.25mm)

