

Technical datasheet: FT-41T-1.0A1-478

Specifications:

Resonant Frequency	1.0kHz \pm 0.5kHz
Max Resistance (Zr)	1000 Ω
Capacitance	75000nF \pm 30%nF

Dimensions:

Type A: (D: \varnothing 41mm, d: \varnothing 25mm, T: 0.23mm, t: 0.10mm)

