


Technical datasheet: KPI-G3020-K6277

Specifications:

Operating Temperature	-20°C to +60°C
Storage Temperature	-30°C to +70°C
Rated Voltage	12VDC
Operating Voltage	3VDC to 20VDC
Max. Rated Current	15mA at 12VDC
Resonant Frequency	2.9kHz \pm 0.5kHz
Min SPL	90dB / 12VDC / 30cm
Weight	7g
Case Material/Color	ABS/Black
Tone Nature	Continuous

Dimensions:



Frequency Response:

