

# Technical datasheet: FT-41G-1.0A1-479

## Specifications:

Resonant Frequency	1.0kHz $\pm$ 0.5kHz
Max Resistance (Zr)	800 $\Omega$
Capacitance	75000nF $\pm$ 30%nF

## Dimensions:

Type A: (D:  $\varnothing$ 41mm, d:  $\varnothing$ 25mm, T: 0.23mm, t: 0.10mm)

