


# Technical datasheet: KPI-G4214L-K6286

## Specifications:

Operating Temperature	-20°C to +60°C
Storage Temperature	-30°C to +70°C
Rated Voltage	5VDC
Operating Voltage	2VDC to 8VDC
Max. Rated Current	20mA at 5VDC
Resonant Frequency	2.8kHz $\pm$ 0.5kHz
Min SPL	96dB / 5VDC / 30cm
Weight	13g
Case Material/Color	ABS/Black
Tone Nature	Continuous

## Dimensions:



## Frequency Response:

