


Technical datasheet: KP1634SP3-5829

Specifications:

Input power	Rated 0.5W / Max. 0.8W
Impedance	$8\Omega \pm 15\% \Omega$ (1Vrms at 1.5kHz)
Frequency Range	0Hz to 20kHz
Resonant Frequency	900Hz \pm 20% Hz
Distortion	<10% Max. at 2kHz/2Vrms
Out-diameter	$\varnothing 16\text{mm}$
Height	3.5mm
Weight	1.8g
SPL	90dB \pm 3dB (0.1W/0.1M at average 0.8,1.0,1.2,1.5kHz)
Buzz and Rattle	No audible buzzes, rattles when 2.0V sine wave signal is swept at frequency range.

Dimensions:



Frequency Response:

