

# Technical datasheet: FT-15T-6.0A1-464

## Specifications:

Resonant Frequency	6.0kHz $\pm$ 0.5kHz
Max Resistance (Zr)	500 $\Omega$
Capacitance	14000nF $\pm$ 30%nF

## Dimensions:

Type A: (D:  $\varnothing$ 15mm, d:  $\varnothing$ 11mm, T: 0.23mm, t: 0.10mm)

