

Voyager Sigma

96233813 VOYAGER SIGMA LED E3M WHI

incl. LED	1W LED	EN 60598-2-22	IP40			650°C	T _a 5/35
-----------	--------	---------------	------	---	---	-------	---------------------

Versatile exit sign with low-maintenance LED option

A self-contained, maintained emergency exit sign for 1 x 1W LED strip giving 3 hours manual test emergency operation. IP40, Class I electrical. Body in polycarbonate, finished white. Diffuser in polycarbonate. Can be wall mounted with 20mm conduit or rear back box entry. Legend panels required to be ordered separately in either ISO or EU formats. Complete with LED strip


Dimensions: 327 x 65 x 197 mm

Total power: 4 W

Weight: 1.4 kg



TLG_VSIG_F_P2.jpg



TLG_VYSG_M_LD1.wmf

Lamp position:STD - standard

Lamps:1 x LED / 1W

Total luminous flux:45 lm

Ballast:LED_Con Tridonic EM powerLED Basic

Connected Load:4 W Lambda = 0.95