


## Technical datasheet: KPMB-G2315L1-K6439

### Specifications:

Operating Temperature	-20°C to +60°C
Storage Temperature	-30°C to +70°C
Rated Voltage	1.5VDC
Operating Voltage	1.3V~2VDC
Max.Rated Current	20mA
Resonant Frequency	400Hz±100Hz
Min SPL	70dB at 1.5VDC/20cm
Response Time	50ms
Tone Nature	Continues
Weight	10g
Case Material/Color	ABS/Black

### Dimensions:



### Frequency Response

