

Technical datasheet: PCT-G4546E-K8481

Specifications:

Operating Temperature Range	-40°C to +60°C
Storage Temperature Range	-40°C to +60°C
Capacitance at 100Hz	≤ 273 nF
Sound Pressure Level	90dB at 12Vp-p/ 3.3KHz/ 30cm
Max. Input Voltage	30Vp-p Square Wave
Housing Material/ Color	PA66/ Black

Dimensions:

