



6	Contact Terminals	Brass	Silver Ptd.	7
5	7P Housing	PA66		1
4	Strain Boot	PVC		1
3	Setscrew	Steel	Nickel Ptd.	1
2	"T" Cable Holder	Steel	Nickel Ptd.	1
1	Shell Cover	Zn Alloy	Nickel Ptd.	1
No.	Description	Material	Treat	Q'ty

Specifications

rating : 100V AC 1A MAX
 contact resistance : pins-30mΩ MAX; shell-50mΩ MAX
 Insulation resistance : MIN 100 MEGΩ @500V DC
 voltage withstand : 250V AC R.M.S. for 1 minute

Artikelnummer	Artikeltext
734812	DIN Normkupplung mit Renkverschluss, 7-polig