




Product information ELST 3308 RV FM 8 05

Industrial Connecting Solutions:Archive - Industrial Connectors:Circular connectors E-series M8 (Archive):with screw locking:Appliance socket and appliance connector for front panel mounting:ELST 3308 RV FM 8 05

<http://www.e-catalog.beldensolutions.com/link/57078-24228-62529-24238-24243-24248-37243/en/conf/ui/state>

| | |
|--|---|
| Name | ELST 3308 RV FM 8 05 |
| |  |
| | Front-mounting appliance connector with stranded wire, snap or screw locking, M8 x 0.5 mounting thread, metal casing, O-ring included |
| Delivery informations | |
| Availability | no longer available |
| Product description | |
| Description | Front-mounting appliance connector with stranded wire, snap or screw locking, M8 x 0.5 mounting thread, metal casing, O-ring included |
| Type | ELST 3308 RV FM 8 05 |
| Order No. | 933 146-001 |
| Type of contact | male |
| Number of contacts | 3 |
| Cable material | PVC |
| Cable length | 0.5 m |
| Conductor size | 0.25 mm ² |
| Standard | IEC 61076-2-101 (Ed. 1)/ IEC 60947-5-2 |
| Housing Color | metallic |
| Technical data | |
| Pin dimensions | 1 mm |
| Wire stranding | 14 x 0.15 mm |
| Rated voltage | AC/DC 60 V |
| Rated current | 3 A |
| Material | |
| Contact material | Cu Zn |
| Contact surface material | Au |
| Contact bearer material | PA black |
| Housing material | Cu Zn/Ni |
| O-Ring | NBR |
| Environmental conditions | |
| Protection class (IEC 60529) | IP 67 (with snap locking), |
| Pollution severity | 3 |
| Temperature range | -25 °C to +90 °C |
| Inflammability class | |
| Contact bearer | 94 V-2 |
| Approvals | |
| UL | UL |
| Packaging unit | |
| Packaging unit | 100 pieces |
| Scope of delivery and accessories | |
| Accessories to order separately | fastening nut ELST M M8, order no. 734 032-001 |



HIRSCHMANN


A BELDEN BRAND

Industrial Connecting Solutions:Archive - Industrial Connectors:Circular connectors E-series M8 (Archive);with screw locking:Appliance socket and appliance connector for front panel mounting:ELST 3308 RV FM 8 05

<http://www.e-catalog.beldensolutions.com/link/57078-24228-62529-24238-24243-24248-37243/en/conf/uistate>

Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.