



4	8P 270 Housing	PA66		1
3	Terminals	Brass	Silver Ptd.	8
2	Negative Contactor	Copper	Nickel Ptd.	1
1	Shield Cover	Zn Alloy	Nickel Ptd.	1
No.	Description	Material	Treat	Qty

Specifications rating :

100V AC 4A MAX

contact resistance :

pins-30mΩ MAX; shell-50mΩ MAX

Insulation resistance :

MIN 100 MEGΩ @500V DC

voltage withstand :

250V AC R.M.S. for 1 minute

Artikelnummer	Artikeltext
735315	DIN Norm-Einbaubuchse mit Renkverschluss, 8-polig, 270°