

Plug-in card block - SKBI 64/C64 - 2263036

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug-in card block, Nominal current: 1 A, Number of positions: 64, Pitch: 2.54 mm, Connection method: Screw connection, Color: green

Key commercial data

package_quantity	1
GTIN	4017918053888

Technical data

Dimensions

Length	66 mm
Height	162 mm
Width	118 mm
Pitch	2.54 mm
Hole diameter	4.2 mm

General

Range of articles	SKBI 64
Connection in acc. with standard	EN-VDE
Nominal current I_N	1 A
Nominal voltage U_N	125 V (in acc. with DIN VDE 0110/Gr.B)
Nominal cross section	2.5 mm ²
Stripping length	8 mm
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm
Number of positions	64

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

Plug-in card block - SKBI 64/C64 - 2263036

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260710
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002642
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

GOST / GOST /

Approval details




accessories

SF-SKBI 64 - 2263007

Plug-in card block - SKBI 64/C64 - 2263036

Drawings

Dimensioned drawing



Plug-in card block - SKBI 64/C64 - 2263036

Schematic diagram

