



SPECIFICATION:
Poles: 4
Voltage rating: 250VAC/VDC
Current rating: 7AMP AC/DC
Dielectric with standing: 1,500VAC for 1 min.
Insulation resistance: 1,000 megohms min.
Temperature range: -25 °C to 85 °C
Material:
Housing: Nylon 66 UL 94V-2
Terminal: Brass / tin plated

DATE	REVISION	APPROVAL BY	DIMENSION	mm ±0.2	MODEL	742236
			DRAW BY	Cherry	NAME	Computer connector
			APPROVAL BY	C.CHOY		
			DATE	26-July-2016		