

SAUTER AHMO D02

KERN

Test block type D/DC, accuracy ≥ 4 HL, $\varnothing$ 90 mm (± 1 mm), net weight approx. 2.7 kg, hardness range 790 ± 40 HL

Pictograms

STANDARD



Category

Brand	Sauter
Product category	Measurement technology
Product group	Hardness test block

Construction

Dimension housing (W×D×H)	90×90×52 mm
Dimensions completely mounted (W×D×H)	90×90×52 mm
Material	steel

Services (optional)

Article number for factory calibration	961-132
--	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	90×90×54 mm
Shipping method	Parcel service
Net weight approx.	2,6 kg
Gross weight approx.	2,8 kg
Shipping weight	2,71 kg

Product information

GTIN/EAN number	4045761125834
REACH classification	no prohibited substances

