

KERN ALJ160-4A

Analysenwaagen-Serie mit hohen Wägebereichen, auch mit Eichzulassung [M]



Counting

Counting resolution:	320000
Minimum piece weight at piece counting (Laboratory):	0,500 mg
Minimum piece weight at piece counting (Normal):	5 mg
Reference weight:	yes

Functions

Counting function:	yes
Density determination function:	yes
Peak function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Standby function:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Input voltage:	country-dependent
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Service

DAkkS Certificate:	963-101
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Analytical balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	515 x 400 x 630 mm
Gross weight:	9,250 kg
Net weight:	6,500 kg
Shipping method:	Parcel service

Measuring system

Adjustment options:	External calibration Internal calibration (auto) Internal calibration (manual)
---------------------	--

Linearity:	0,300 mg
------------	----------

n/a:	200 mg
------	--------

Readout [d]:	0,100 mg
--------------	----------

Recommended adjusting weight:	150 g (E2)
-------------------------------	------------

Reproducibility:	0,100 mg
------------------	----------

Resolution:	1.600.000
-------------	-----------

Stabilisation time:	4 s
---------------------	-----

Tare range:	160 g
-------------	-------

Warm up time:	8 h
---------------	-----

Weighing range [Max]:	160 g
-----------------------	-------

Weighing system:	Force compensation
------------------	--------------------

Weighing units:	ct dwt g gn lb mg mo oz ozt tl (HK) tl (Singap. Malays) tl (Tw)
-----------------	--

Display

Display digit height:	1,700 cm
-----------------------	----------

Technical data about verification

Verification class:	I (ohne Bauartzulassung)
---------------------	--------------------------

KERN ALJ160-4A

Analysenwaagen-Serie mit hohen Wägebereichen, auch mit Eichzulassung [M]



Construction

Casing material:	Plastic
Dimensions draft shield (WxDxH):	190 x 195 x 225 mm
Dimensions housing (WxDxH):	210 x 340 x 330 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing space (WxDxH):	160 x 140 x 205 mm
Weighing surface (d):	80