

KERN CM50-C2N

Die Praktische mit Klappdeckel

KERN®



Category

Brand:	KERN
Category:	Balances

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	135 x 203 x 30 mm
Gross weight:	300 g
Net weight:	170 g
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	85 x 130 x 25 mm
Material weighing plate:	Plastic
Weighing surface (WxD):	50 x 40 mm

Measuring system

Adjustment options:	External calibration
Linearity:	6 mg
Readout [d]:	2 mg
Recommended adjusting weight:	5 g (M1)
Reproducibility:	4 mg
Resolution:	5000
Stabilisation time:	3 s
Warm up time:	10 min
Weighing range [Max]:	10 g
Weighing system:	Strain gauge
Weighing units:	ct g

Display

Display digit height:	9 mm
-----------------------	------

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Operating time:	30 h
-----------------	------

Service

Adjustment at the location of installation: 961-247

DAkKS Certificate: 963-127