

KERN EMB 2000-2

Einsteiger-Laborwaage mit enormen Wägeleistungen



n/a: Mains adapter external

Power supply

Operating time: 12 h
Operating time (Backlight off): 50 h
Rechargeable battery: Rchrg. battery optional

Service

DAkkS Certificate: 963-127

Category

Brand: KERN
Category: Balances
Product Group: School balance

Packaging & shipping

Delivery: 24 h
Dimensions packaging (WxDxH): 220 x 290 x 150 mm
Gross weight: 1,258 kg
Net weight: 891 g
Shipping method: Parcel service

Construction

Casing material: Plastic
Dimensions housing (WxDxH): 170 x 240 x 54 mm
Material weighing plate: Plastic
Weighing surface (d): 150

Measuring system

Adjustment options: External calibration
Linearity: 50 mg
Readout [d]: 10 mg
Recommended adjusting weight: 2 kg (F1)
Reproducibility: 10 mg
Resolution: 200000
Stabilisation time: 2,500 s
Warm up time: 2 h
Weighing range [Max]: 2 kg
Weighing system: Strain gauge
Weighing units: dwt g oz oz

Display

Display digit height: 1,500 cm

Functions

Suspended weighing: Hook

Environmental conditions

Maximum humidity: 80 %
Maximum operating temperature: 35 °C
Minimum ambient temperature: 5 °C

Power supply

Charging time: 10 h