

KERN EMB 3000-1

Einsteiger-Laborwaage mit enormen Wägeleistungen



n/a: Mains adapter external

Power supply

Operating time: 12 h
Operating time (Backlight off): 50 h
Rechargeable battery: Rchrg. battery optional

Service

Adjustment at the location of installation: 961-247

DAkkS Certificate: 963-127

Category

Brand: KERN
Category: Balances
Product Group: School balance

Packaging & shipping

Delivery: 24 h
Dimensions packaging (WxDxH): 265 x 207 x 116 mm
Gross weight: 743 g
Net weight: 510 g
Shipping method: Parcel service

Construction

Casing material: Plastic
Dimensions housing (WxDxH): 170 x 240 x 39 mm
Material weighing plate: Plastic
Weighing surface (d): 150

Measuring system

Adjustment options: External calibration
Linearity: 300 mg
Readout [d]: 100 mg
Recommended adjusting weight: 3 kg (M1)
Reproducibility: 100 mg
Resolution: 30000
Stabilisation time: 3 s
Warm up time: 2 h
Weighing range [Max]: 3 kg
Weighing system: Strain gauge
Weighing units: dwt g oz oz

Display

Display digit height: 1,500 cm

Functions

Suspended weighing: Loop

Environmental conditions

Maximum humidity: 80 %
Maximum operating temperature: 35 °C
Minimum ambient temperature: 5 °C

Power supply

Charging time: 10 h