



Discover more details and matching accessories online!

Universal digital force gauge for tensile and compressive force measurements with external load cell

Features

- Turnable display with backlight
- **1** USB interface for data transfer and power supply as standard
- Data interface RS-232 as standard
- Selectable measuring units: N, kN, kgf, tf
- Peak-Hold function to capture the peak value or Track function for continuous display of measurement
- Measuring with tolerance range (limit-setting function): Upper and lower limit adjustable, in pull and push direction.
The process is supported by an audible and visual signal

- Auto-Power-Off
- Internal memory for up to 10 measurement values
- Mini Statistics Kit: calculates the average result from up to 10 stored measured values, as well as min., max., n
- Tension loops and compression plates are included in delivery
- **2** Delivered in a robust carrying case

Technical data

- Transfer rate to PC: approx. 25 measured values per second
- Measuring precision: 0,5 % of [Max]
- Overload protection: 150 % of [Max]
- Overall dimensions W×D×H 45×25×0 mm
- Rechargeable battery pack integrated, as standard, operating time up to 40 h without backlight, charging time approx. 120 min
- External mains adapter, for connection to the USB-C connector, standard
- Cable length approx. 3 m
- Net weight approx. 1,6 kg

STANDARD

OPTION

Model	Measuring range [Max] kN	Readability [d] N	Option calibration certificate DAkkS accr. (≤ 5 kN) / Factory calibration certificate (> 5 kN)		
			Tensile Force	Compressive Force	Tensile/Compressive Force
SAUTER			KERN	KERN	KERN
FH 1K	1	0,5	963-162	963-262	963-362
FH 2K	2	1	963-162	963-262	963-362
FH 5K	5	1	963-163	963-263	963-363
FH 10K	10	5	961-164	961-264	961-364
FH 20K	20	10	961-164	961-264	961-364
FH 50K	50	10	961-165	961-265	961-365
FH 100K	100	50	961-166	961-266	961-366

Further calibration options on request