

# KERN FKB 15K1A

Tischwaage bis 65 kg mit großer Wägeplatte



## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

## Power supply

Charging time:	10 h
n/a:	CH EURO UK US
Operating time:	12 h
Operating time (Backlight off):	10 h
Operating time (Backlight on):	8 h
Rechargeable battery:	Rchrg. battery optional

## Service

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

## Category

Brand:	KERN
Category:	Balances
Product Group:	Bench scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	470 x 470 x 190 mm
Gross weight:	6,270 kg
Net weight:	5,340 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	350 x 390 x 120 mm
Dimensions of weighing plate (WxDxH):	340 x 240 x 21 mm
Material weighing plate:	stainless steel
Weighing surface (WxD):	340 x 240 mm

## Measuring system

Adjustment options:	External calibration
Linearity:	3 g
Readout [d]:	1 g
Recommended adjusting weight:	15 kg (M1)
Reproducibility:	1 g
Resolution:	15000
Stabilisation time:	3 s
Warm up time:	30 min
Weighing range [Max]:	15 kg
Weighing system:	Strain gauge
Weighing units:	dwt g kg lb mo oz ozt tl (HK) tl (Tw) tol

## Display

Display digit height: 2,500 cm

## Counting

Counting resolution:	7500
Minimum piece weight at piece counting (Laboratory):	2 g
Minimum piece weight at piece counting (Normal):	20 g

## Functions

Counting function:	yes
Percentage determination:	yes
Suspended weighing:	Hook
Vibration-free weighing (Animal weighing program):	yes