

# KERN FOB6K2

Edelstahlwaage mit erhöhtem Feuchteschutz und Eichzulassung [M]



## Service

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

## Category

Brand: KERN

Category: Balances

Product Group: Bench scale

## Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 400 x 250 x 110 mm

Gross weight: 2,590 kg

Net weight: 2,130 kg

Shipping method: Parcel service

## Construction

Casing material: stainless steel

Dimensions housing (WxDxH): 180 x 235 x 60 mm

Level indicator: yes

Material weighing plate: stainless steel

Revolving screw feet: yes

Weighing surface (WxD): 175 x 165 mm

## Measuring system

Adjustment options: External calibration

Linearity: 4 g

Readout [d]: 2 g

Recommended adjusting weight: 5 kg (M2)

Reproducibility: 2 g

Resolution: 3000

Stabilisation time: 2 s

Warm up time: 10 min

Weighing range [Max]: 6 kg

Weighing system: Strain gauge

Weighing units: g lb oz

## Display

Display digit height: 2,500 cm

## Environmental conditions

Maximum humidity: 95 %

Maximum operating temperature: 40 °C

Minimum ambient temperature: -10 °C

Minimum humidity: 25 %

## Power supply

Charging time: 8 h

n/a: CH EURO

Operating time (Backlight off): 24 h

Rechargeable battery: Rchrg. battery optional