

# KERN HFB 150K50

Die professionelle Alternative bis 600 kg mit rückwärtiger Zweitanzeige



n/a: Mains adapter external

## Power supply

Operating time (Backlight off): 40 h

Operating time (Backlight on): 30 h

## Service

Adjustment at the location of installation: 961-249

DAkKS Certificate: 963-129H

## Category

Brand: KERN

Category: Balances

Product Group: Crane scale

## Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 257 x 435 x 210 mm

Gross weight: 3,158 kg

Net weight: 2,188 kg

Shipping method: Parcel service

UN number: 2800

## Construction

Casing material: Plastic

Dimensions housing (WxDxH): 162 x 123 x 158,5 mm

Dimensions of display device (WxDxH): 162 x 123 x 158,5 mm

Overall dimensions mounted (WxDxH): 162 x 123 x 390 mm

## Measuring system

Adjustment options: External calibration

Linearity: 100 g

Precision (of [Max]): 0,002

Readout [d]: 50 g

Recommended adjusting weight: 150 kg (M3)

Reproducibility: 50 g

Resolution: 3000

Stabilisation time: 2 s

Tare range: 149,950 kg

Warm up time: 10 min

Weighing range [Max]: 150 kg

Weighing system: Strain gauge

Weighing units: kg lb

## Display

Additional Display possible: no

Display digit height: 2,500 cm

## Functions

Data hold function: yes

## Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 40 °C

Minimum ambient temperature: 0 °C

Minimum humidity: 0 %

## Power supply

Charging time: 14 h

Input voltage: 110 V - 230 V AC

n/a: CH EURO UK