

KERN MGB 150K100

Designer personal scale with glass weighing plate



Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	360 x 360 x 90 mm
Gross weight:	2,517 kg
Net weight:	2,001 kg
Shipping method:	Parcel service
UN number:	3091

Construction

Casing material:	Plastic
Overall dimensions mounted (WxDxH):	290 x 290 x 40 mm

Measuring system

Adjustment options:	Calibration not possible
Linearity:	500 g
Readout [d]:	100 g
Reproducibility:	200 g
Resolution:	1500
Warm up time:	10 min
Weighing range [Max]:	150 kg
Weighing system:	Strain gauge
Weighing units:	kg lb

Display

Display digit height:	2,500 cm
-----------------------	----------

Environmental conditions

Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Service

Adjustment at the location of installation: 961-249

DAkkS Certificate:	963-129
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Personal floor scale