

KERN PCD250-3

Hochauflösende Präzisionswaage mit abnehmbarem Auswertegerät für maximale Flexibilität



Functions

Counting function:	yes
Peak function:	yes
Percentage determination:	yes
Vibration-free weighing (Animal weighing program):	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Charging time:	10 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK US

n/a: Mains adapter external

Power supply

Operating time:	12 h
Operating time (Backlight off):	24 h
Operating time (Backlight on):	12 h
Rechargeable battery:	Rchrg. battery optional

Service

DAkkS Certificate:	963-127
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	238 x 357 x 180 mm
Gross weight:	1,800 kg
Net weight:	1,100 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	1,200 m
Casing material:	Plastic
Dimensions draft shield (WxDxH):	157 x 157 x 80 mm
Dimensions housing (WxDxH):	165 x 280 x 75 mm
Dimensions of display device (WxDxH):	140 x 75 x 46 mm

Measuring system

Adjustment options:	External calibration
Linearity:	5 mg
n/a:	4 g
Readout [d]:	1 mg
Recommended adjusting weight:	250 g (F1)
Reproducibility:	2 mg
Resolution:	250000
Stabilisation time:	3 s
Tare range:	250 g
Warm up time:	2 h
Weighing range [Max]:	250 g
Weighing system:	Strain gauge
Weighing units:	ct dwt ffa g gn mo oz ozt tl (HK) tl (Tw) tol

Display

Display digit height:	2,100 cm
-----------------------	----------

Counting

Counting resolution:	125000
Minimum piece weight at piece counting (Laboratory):	2 mg
Minimum piece weight at piece counting (Normal):	20 mg

KERN PCD250-3



Hochauflösende Präzisionswaage mit abnehmbarem Auswertegerät für maximale Flexibilität

of stand:	25 cm
Level indicator:	yes
Overall dimensions mounted (WxDxH):	165 x 280 x 75 mm
Revolving screw feet:	yes
Weighing space (WxDxH):	146 x 146 x 80 mm
Weighing surface (d):	105