

# KERN SFB50K5LHIP

Edelstahl-Plattformwaage mit Staub- und Spritzwasserschutz IP65 und Eichzulassung [M]



Weighing with tolerance range: yes

## Environmental conditions

Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	10 %

## Power supply

Charging time:	12 h
Input voltage:	110 V - 230 V AC
n/a:	CH EURO UK US

n/a: Mains adapter external

## Power supply

Operating time (Backlight off):	35 h
Operating time (Backlight on):	20 h

## Service

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

## Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	465 x 790 x 230 mm
Gross weight:	14,700 kg
Net weight:	12,400 kg
Shipping method:	Parcel service
UN number:	2800

## Construction

Cable length of display device:	3 m
Dimensions of display device (WxDxH):	266 x 165 x 96 mm
Dimensions of weighing plate (WxDxH):	400 x 300 x 128 mm
of stand:	40 cm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	400 x 460 x 590 mm

## Measuring system

Adjustment options:	External calibration
Linearity:	5 g
Readout [d]:	5 g
Recommended adjusting weight:	50 kg (M1)
Reproducibility:	5 g
Resolution:	10000
Stabilisation time:	2 s
Warm up time:	30 min
Weighing range [Max]:	50 kg
Weighing system:	Strain gauge
Weighing units:	kg

## Display

Display digit height: 5,200 cm

## Functions

Counting function:	yes
Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes

# KERN SFB50K5LHIP



Edelstahl-Plattformwaage mit Staub- und Spritzwasserschutz IP65 und Eichzulassung [M]

Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	400 x 300 mm