

KERN TCB 200-1

Jetzt geht's rund - Wiegen im Taschenformat

KERN®



Category

Brand:	KERN
Category:	Balances
Product Group:	Pocket balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	96 x 120 x 21 mm
Gross weight:	105,600 g
Net weight:	50,400 g
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Material weighing plate:	Plastic
Weighing surface (d):	80

Measuring system

Adjustment options:	External calibration
Linearity:	200 mg
Readout [d]:	100 mg
Recommended adjusting weight:	100 g (M3)
Reproducibility:	100 mg
Resolution:	2000
Stabilisation time:	2 s
Warm up time:	10 min
Weighing range [Max]:	200 g
Weighing system:	Strain gauge
Weighing units:	g

Display

Display digit height:	9 mm
-----------------------	------

Environmental conditions

Maximum humidity:	85 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Operating time:	10 h
-----------------	------

Service

Adjustment at the location of installation: 961-247

DAkkS Certificate: 963-127