









Coax cable connection for C4L6400-EoC-P extended port





Wire Type / Bandwidth (Mbps)	10	20	30	40	50	60	70	80	92	94	94	94	94	94
Coax CCTV Solid Copper RG-11 14 AWG	4999	4572	4180	3760	3380	3040	2700	2330	1615	200	100	50	20	10
Coax CCTV Solid Copper RG-59/U 20 AWG	2499	2377	2180	1990	1790	1580	1400	1220	914	200	100	50	20	10
Coax CCTV Solid Copper RG-59/U 22 AWG	2042	1920	1760	1600	1460	1290	1128	990	762	200	100	50	20	10
Coax CCTV Solid Copper RG-6 18 AWG	3018	2865	2670	2480	2250	2000	1745	1494	1036	200	100	50	20	10



Remote PD Power(Watts)	Coaxial Cable Distance(meters) of RG6/ 18 AWG	Coaxial Cable Distance(meters) of RG59/ U22 AWG	Coaxial Cable Distance(meters) of RG59/ U20 AWG	Coaxial Cable Distance(meters) of RG11/ 14 AWG
5	954	502	681	2384
10	571	301	408	1428
15	407	214	291	1018
20	316	166	226	790
25	258	136	184	645
30	218	115	156	545
35	188	99	135	471
40	166	87	119	415

