

CAB CAB PC 403018 T



Sample photo

Order symbol: CAB PC 403018 T
Product nbr: 8113050
Description: Cabinet, PC
Remarks: Latches on the long side

EAN: 6418074020215
EI. number:
 Finland: 3424164
 Electric No. 8212020252
 Denmark:
 Electric No. Italy: 7822040
 Electric No. Sweden: 2539945

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:	Length	Width	Height	Accessories:
mm:	400	300	180	EKIV 43 PL Mounting plate, Plastic
inch:	15.7	11.8	7.1	EKIV 27 DIN-35 Mounting rail

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	Smoked grey
Gasket material:	Polyurethane

Temperatures:

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Accessories:

EKIV 43	Mounting plate
---------	----------------

DS35270E1	DIN-35 Mounting rail
EKIV 37	DIN-35 Mounting rail
DS35370E1	DIN-35 Mounting rail
FP A 43	Swing-out door/Front plate
MB 12225 AL	Swing door set
FP 43	Front plate
FP 12x2-43	Front plate
FP 12x3-43	Front plate
DRF 43/44	DIN rail frame set

Rating:

- Ingress Protection (EN 60529): IP65
- Impact Resistance (EN 62262): IK08
- Electrical insulation: Totally insulated
- Halogen free (DIN/VDE 0472, Part 815): 1
- UV resistance: UL 508
- Flammability Rating: UL 746C 5"
- Glow Wire Test (IEC 695-2-1) °C: 960

Certificates:

- SGS Fimko
- Gost R

