



External Drive Type
(A)

Self Drive Type
(B)

Conrad Best.-Nr.	NO	PART NO	Max Input Voltage	Fr (KHz)	Zr (ΩMAX)	Cp	Dimension(mm)			
							D	d	T	t
818274	<u>H21205C9</u>	FT-12T-6.5A1-K883	30Vp-p	6.5±1.0	800	13000PF±30%	φ12	φ9	0.14	0.08

The ceramics' curie temperature of this piezo element is 260 degree C.

Voltage vs Freq



LMS

Map

1: Sweep

Notes

LMS

4.5.0.332
二月-27-2003

Person:
Company: 宁波凯普电子有限公司

Project: FT-12T-6.5A1
File: FT-12T-6.5A1.lib

Nov 16, 2015
Mon 1:17 pm

LINEAR X
S Y S T E M S