

Product Specifications:

Camera Sensor : 1.3 Mega Pixel CMOS

Field of View : 54

Focal Length : 20" to infinity

Macro Effect : 20" with background unfocused

Photo Rate Settings : 6 predetermined time settings, 1 custom

- 1st: 1 minute
- 2nd: 5 minutes
- 3rd: 30 minutes
- 4th: 1 hour
- 5th: 4 hours
- 6th: 24 hours
- 7th: Customized setting is created by the user through Brinno software

Time : All photos are time and date stamped

Format : A JPEG image stored in a single folder for easy playback and viewing as an AVI file.

Portable Memory Storage : Up to 8GB on any standard USB Flash Drive (2GB USB Flash Drive included)

System Memory : 8 MB SD RAM

Power Source : 4 AA Batteries (Included)

length of battery usage : 4 - 6 Months depending on time setting

Size (DxWxH) inches : 2.08 x 3.66 x 7.55

Weight : 0.75lbs (without batteries)

Housing Material : Weather resistant plastic

Accessories : Custom designed adjustable mounting stake