



**Designation:** 10616

**Battery Requirement:** 2 x AA

**Bulb required:** Nichia 5mm White LED

**Luminous intensity:** 6 lumens or 121 cd

**Range:** 11m (calculated distance at maximum luminous intensity with an illuminance of 1lux).

**Weight:** 78g (without batteries).

**Material:** Silicon  
 SAN (Acrylonitrile Styrene)  
 ABS (Acrylonitrile Butadiene Styrene)  
 PP (Polypropylene)  
 All contact parts made of bronze or brass  
 Contact spring in the screw cap, nickel plated steel.

<b>Dimensions (mm):</b>	<b>A</b>	<b>179.7</b>
	<b>B</b>	<b>157.5</b>
	<b>C</b>	<b>88.8</b>
	<b>D</b>	<b>45.5</b>
	<b>E</b>	<b>30</b>

**Run Time: 25 hours (with VARTA alkaline battery)**

**Features:**

- Push switch (on/off)
- Magnifier lens provide long beam
- Gelly grip handle
- DC/DC regulator
- 1 meter impact resistant
- Hook for hang

