



Designation:	11628 101 421
Battery Requirement:	3 x AAA
Bulb required:	Taiwanese Profi Light 1W HP LED
Luminous intensity:	High mode: 80 lumens or 553 cd Low mode: 30 lumens
Range:	25,0m (calculated distance at maximum luminous intensity with an illuminance of 1lux).
Weight:	102g (without batteries).

Material:	Aluminium (Anodized)
	Silicon rubber
	ABS (Acrylonitrile Butadiene Styrene)
	PC (Polycarbonate)
	All contact parts made of aluminium or steel
	Contact spring nickel or Zinc plated steel.

Dimensions (mm):	A	114,4
	B	37,9
	C	35,1
	D	27,5

Run Time:	5 hours (with VARTA alkaline battery on high mode)
	20 hours (with VARTA alkaline battery on low mode)

Features:	Push switch (Low / High / Off)
	Silicon rubber
	9 feet impact resistant
	Water resistant
	Lanyard