

- Product Data Sheet -



Article **Liberty Aqua Diver - Headlamp**

Art. number **LXL10000W4**  
 Manufacturer **LiteXpress**

Color **Black/ Yellow**  
 Material **Plastic/ Rubber**

Recom. Retail Price **34,95 €**



Description: The LiteXpress Liberty Aqua is a 30 m waterproof, extremely robust outdoor lamp with high-performance LED and 146 lumens of light intensity. Thanks to the multifaceted reflector, it can illuminate a wide area. The two light modes (high and low) can be selected via the magnetic rotary switch. Apart from the luminous efficacy, the long life of the lamp is also impressive. 4 new AA LR6 batteries or freshly charged batteries of the same type can last up to 47 hours in continuous operation. The sturdy plastic housing safely protects the robust lighting technology.

Features - Insulation Products

Insulation effect		Sealing		Capacity	
Cold in hours	n/a	Type of lid	n/a	Capacity in liters	n/a
Hot in hours	n/a	Filling hole in cm	n/a		

Specials

Features - Flashlights

Battery/Rech. Battery		Brightness		Other	
Type	AAA	Max lumens	146	Light source	LED
Amount required	4	Min lumens	36	Amount of modes	2
Weight battery in gr	11,00			Modes / functions	High, Low
Total weight in gr	44,00	Luminous range			
Batteries included?	yes	Max meters	127	Special features	
		Min meters	54		
		Lighting duration			
		Max <sup>1</sup> h	1,5		
		Min <sup>1</sup> h	47,0		

<sup>1</sup> Max relates to the lighting duration in highest light mode and Min to the duration in lowest light mode

Dimensions / Others

Inner Carton		Product		Other	
Length in cm	26,70	Length in cm	7,10	Country of Origin	China
Width in cm	32,00	Width in cm	10,70	Customs tariff num.	8513100000
Height in cm	19,20	Height in cm	3,90	EAN13 number	48970101776644
Weight in gr	2.140,00	Diameter	-		
Units	6	Weight in gr	147,00		
Outer Carton		Product packaging		Information - Multitools / Knives	
Length in cm	33,50	Length in cm	6,00	Total length in cm	n/a
Width in cm	60,00	Width in cm	27,70	Handle length in cm	n/a
Height in cm	59,00	Height in cm	17,20	Blade length in cm	n/a
Weight in gr	14.300,00	Weight in gr	260,00	Tools included	n/a
Units	36	Units	1		