

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SHV	52002600 14.11.2013

Watertight
Gentle cable clamping
Robust
High strain relief



Optimum strain relief



Robust



Waterproof

Application range

Watertight cable gland with conical sealing element.
Pumps
Floater switches

Design

PG connection thread

Note

Counter nut to be used: SKINDICHT® SM

Suitable accessory: SKINDICHT® SHV sealing cones

Example order designation: SHV 13.5/9/913.5 = PG thread of compression screw9 = PG connection thread9 = clear opening of sealing cone

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size: SHV 13,5/13,5/9

Clamping range ØF (mm): 6,8 - 8,8

SW 1/2 mm: 22

Overall length, C (mm): 33

Thread length, D (mm): 6.5

Pieces / PU: 25

Caution: The installation dimensions
can be found in appendix T21

Material: Body: nickel-plated brass
Sealing cone: CR
O-ring: NBR


Protection rating: IP 68 - 10 bar

Temperature range: -20°C to +80°C



Product Management	Document: SKINDICHT® SHV	1 / 2
--------------------	--------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SHV	52002600 14.11.2013



Product Management	Document: SKINDICHT® SHV	2 / 2
--------------------	--------------------------	-------