

U.I. Lapp GmbH	DATASHEET	
	SKINTOP® DIX	53629480 14.11.2013

Easy insertion of several cables into one gland
Higher packing density allows smaller part construction



Assembly time



Reliability



Temperature-resistant



Application range

For use in SKINTOP® cable glands.

A sealing ring with several holes is used in place of the inner sealing insert.

Note

IP 68 can be achieved when all openings are closed and all bores are optimally occupied, i.e. when using cables with nominal diameter and/or SKINTOP® DIX-DV sealing plugs

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	DIX 29480
PG size:	29
Number of cables x cable Ø:	4 x 8
Pieces / PU:	50
Colour delivered:	natural
Material:	Silicone
Protection rating:	IP 54
Temperature range:	-40°C to +100°C

Product Management	Document: SKINTOP® DIX	1 / 1
--------------------	------------------------	-------